

11190000	DATA SHEET	
Valid from: 05.06.2024	EPIC® H-BE 2.5 CONTACTS MACHINED	

Description

- For inserts and modules of the EPIC® rectangular connectors



Article-Number	Article	Version	Conductor cross-section (mm²)	Cross-section ratio	Surface	Stripping length (mm)
Contacts (silver plated)						
11190000	H-BE 2.5	Male	0,5	0	Ag	8,0
11195000	H-BE 2.5	Female	0,5	0	Ag	8,0
11190100	H-BE 2.5	Male	0,75 - 1	1	Ag	8,0
11195100	H-BE 2.5	Female	0,75 - 1	1	Ag	8,0
11190200	H-BE 2.5	Male	1,5	2	Ag	8,0
11195200	H-BE 2.5	Male	1,5	2	Ag	8,0
11190300	H-BE 2.5	Female	2,5	3	Ag	8,0
11195300	H-BE 2.5	Male	2,5	3	Ag	8,0
11190400	H-BE 2.5	Female	4,00	Without	Ag	8,0
11195400	H-BE 2.5	Male	4,00	Without	Ag	8,0
Contacts (gold plated)						
11192000	H-BE 2.5	Male	0,5	0	Au	8,0
11197000	H-BE 2.5	Female	0,5	0	Au	8,0
11192100	H-BE 2.5	Male	0,75 - 1	1	Au	8,0
11197100	H-BE 2.5	Female	0,75 - 1	1	Au	8,0
11192200	H-BE 2.5	Male	1,5	2	Au	8,0
11197200	H-BE 2.5	Female	1,5	2	Au	8,0
11192300	H-BE 2,5	Male	2,5	3	Au	8,0
11197300	H-BE 2,5	Female	2,5	3	Au	8,0
11190301	H-BE 2,5	Male	0,14-0,37	1	Au	8,0
11190302	H-BE 2,5	Female	0,14-0,37	1	Au	8,0



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB11190000EN Version: 04	Page 1 of 1
---	---------------------------------------	-------------