44423365	DATA SHEET	LAPP
Valid from: 26.04.2022	EPIC® MHB 2 40A CM	

Description

- Power module 2-pin for compact power transmission
- Crimp connection for permanent vibration-proof contact
- EPIC® MH system is mateable with the market standard
- The mix of different functions is one plug guarantees high flexibility



General characteristics

Contact type	socket
Number of contacts	2
Mating cycles	500
Material	Polyamide, glass fibre-reinforced
Inflammability class acc. with UL 94	V0
Pollution degree	3
Temperatue range	-40° C to +125° C
Termination methods	crimp termination: 1.5 - 10 mm²
Suitable frame	Epic® MH 6 multi-frame Epic® MH 10 multi-frame Epic® MH 16 multi-frame Epic® MH 24 multi-frame
Suitable contacts	Epic® MH 4.0mm contacts

Electrical characteristics


Rated voltage	1000 V (Conductor-PE); 1000 V (Conductor-Conductor)
Contact resistance	< 5 mΩ
Rated impuls voltage	8 kV
Rated current	40 A

Standards/Approvals

cURus	according to UL 1977: in preparation
Fire protection on railway vehicles	according EN 45545-2 requirement sets R22 and R23 hazard level HL1, HL2 and HL3

We reserve all rights according to DIN ISO 16016.

Drawings



Note

Photographs are not to scale and do not represent detailed images of the respective products.

We reserve all rights according to DIN ISO 16016.