

10542000	DATA SHEET	
Valid from: 18.09.2020	EPIC® H-A 32 SS / H-A 32 BS	

Description

- H-A inserts with screw termination up to 2.5 mm² wire cross section.
- Slim connector insert for standard application.
- Easy to service screw connection.
- Universal for current and voltage transmission.



General Characteristics

Series	H-A 32
Version	Male/Female(Article 10531000)
Wire Protection	No
Number of Contacts	32 + 2 PE
Termination Methods	Screw termination: 0.5 - 2.5 mm ² (2.5 mm ² with conductor end sleeves depending on the crimping profile)
Temperature Range	-40°C to +100°C, short-term up to +125°C

Mechanical Characteristics

Cycle of mechanical operation	100
-------------------------------	-----

Electrical Characteristics

Rated Voltage, IEC	400 V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	4 kV
Rated Current, IEC	16 A
Rated Current, UL	14 A
Rated Current, CSA	16 A
Contact Resistance	1,5 - 4 mOhm
Degree of Soiling	3

Materials and Surfaces

Contacts	Copper alloy, hard silver-plated
Insulating Body	PBT
Flammability Class according to UL 94	V0

Approvals

UL-Approval, E-File-Number	E75770
----------------------------	--------

Standard

Safety Standard	IEC 61984, UL 1977, CSA-C22.2 182.3
-----------------	-------------------------------------


Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB10542000EN Version: 02	Page 1 of 3
---	---------------------------------------	-------------

10542000	DATA SHEET	
Valid from: 18.09.2020	EPIC® H-A 32 SS / H-A 32 BS	



Technical Drawings



F



M



10542000	DATA SHEET	
Valid from: 18.09.2020	EPIC® H-A 32 SS / H-A 32 BS	



Industrial machinery and plant engineering



Assembly time



Space requirement

Info

Slim standard insert, easy to connect by screw
Universal for current and voltage transmission

Application range

Machine and equipment manufacturings
Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB10542000EN Version: 02	Page 3 of 3
---	---------------------------------------	-------------