

10423640	DATA SHEET	
Valid from: 25.03.2021	EPIC® ULTRA H-A 3 EGS	

Description

- Innovative metal housing
- For safe connections in the smallest possible space
- EMC protection
- Corrosion-resistant



General characteristics

Series	ULTRA H-A 3
Version	Screw mounted housing angled
Locking mechanism	Single lever
Protection rating (DIN EN 60529)	IP 66 (latched) IP 68 - 1 meter / 10 hours (latched)
Protection rating (NEMA 250, UL50E)	4, 4X, 12 (latched)
Temperature range	-40 °C to +100 °C, short-term up to +125 °C
Holding screws for inserts included	yes

Materials and surfaces

Housing, base material	Zinc die-casting
Housing, surface	Nickel-plated
Lever	Stainless steel
Gasket	NBR
Counter nut	Brass, nickel-plated
Holding screws for inserts	Stainless steel

Standard

Safety Standard	IEC 61984
-----------------	-----------



Approvals

cURus and VDE in preparation.

Creator: TODV1/PDP Released: VACH1/PDP	Document: DB10423640EN Version: 00	Page 1 of 2
---	---------------------------------------	-------------

10423640	DATA SHEET	
Valid from: 25.03.2021	EPIC® ULTRA H-A 3 EGS	

Technical Drawings



Waterproof



Space requirement



Interference signals



Assembly time



Connectors with standart housing



Corrosion resistant



Robust



Good chemical resistance

Info

EMC protection, Corrosion-resistant, Compact, robust metal housings size H-A 3

Application range

In EMC-sensitive environments, For fixed and flexible applications (e.g. machinery building, wind turbines), Construction machinery, Electric motor manufacturing

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/PDP Released: VACH1/PDP	Document: DB10423640EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------