


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.







ADHESIVE TAPE

PRESSURE SENSITIVE TAPE 0.040(1.0) THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.30 lbs(136 g) MAX. WEIGHT ON A CLEAN,DRY,SMOOTH, GREASE-FREE SURFACE.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.


PANDUIT PART NO. *	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT lbs (g) / 100 pcs
ABMM-AT	MINIATURE INTERMEDIATE	0.113 (51.3)

TO APPLY MOUNT

1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL.
2) REMOVE PROTECTIVE LINER.
3) PLACE IN DESIRED LOCATION.
4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS.

NOTES:

* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR EASY REMOVAL OF LINER.
3) MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 180°F(82°C).



ACTUAL SIZE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS: G00239ER_DC_ABMM_AT_08

PANDUIT CORP. TINLEY PARK, ILLINOIS

ABMM-AT
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± ---- (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ± ----

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY: AJV
DATE: 12-23-96
CHK'D:
MAT'L: ABS (ACRYLONITRILE BUTADIENE STYRENE)
SCALE: NONE
DRAWING NO.: GB0239ER
DWG: A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
8	6/29/06	JAD		REMOVE ABM20B	GB0239ER 8		