

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






PANDUIT PART NUMBER	WEIGHT lbs/100 pcs. (g)/100 pcs.	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS	MAX. SCREW SIZE
MBMS-S10 (SEE NOTE 3)	.123 (55.8)	MINIATURE INTERMEDIATE STANDARD	#10 (M5)

D NOTES:

1. MATERIAL: ALUMINUM ALLOY - 3003-H14 (HALF HARD, TEMPER).

E 2. FINISH: CORROSION RESISTANT TCP COATING.

F 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PART NUMBER SUFFIX DESIGNATIONS AND PACKAGE SIZE.



SCALE 1:1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06-26-25	BDK	JADE	DJSL	F. REVISED "SUFFIX/PACKAGE SIZE" NOTE TO REFERNCE PANDUIT.COM. E. REVISED "FINISH" NOTE. D. REMOVE PACKAGE GOOD PART NUMBER NOTE. (SEE NOTE 3) C. INCREASED FROM 0.43 TO 0.44, ROUND OFF. B. ELIMATED DIMENSION 0.62 [15.7] (REF.). A. REBUILD MODEL AND RECREATED DRAWING 'A' TEMPLATE FOR THE CUSTOMER DRAWING.	014246 r00

A

TITLE

MBMS-S10 METAL MOUNT

CUSTOMER DRAWING

ITEM REVISION NAME: G03597GW/08

DATASET FILE NAME: G03597GW_DC/08A GB0239LW CUST. DWG

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .XXX ±

.XX ± ANGLES ±

THIRD ANGLE PROJECTION

PANDUIT

MATERIAL: SEE NOTES 1 & 2

DRAWING NUMBER: GB0239LW

DRAWN BY	DATE	CHK	SCALE	SIZE
JAD	7/27/06	JADE	NTS	A

SHT 1 OF 1

D10100DA/20