

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	DIMENSIONS				MAXIMUM CABLE DIA. in. (mm)	ADHESIVE BACKING	WEIGHT lbs/100 pcs (g)/100 pcs
	A	B	C	D			
ACC62-A	1.12 (28.5)	1.24 (31.4)	.73 (18.5)	0.65 (16.5) (REF)	0.62 (15.7)	RUBBER	0.96 (437)
ACC62-AT						ACRYLIC	
ACC62-AV						HIGH BOND ACRYLIC	





NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01D	2/26/15	RVU	CLW	JHAC	SHOW THE TEAR TABS IN THE CORRECT LOCATION.	GAECN02621
00C	11/6/09	TMSA			ADDED PART NUMBER ACC62-AV.	GB0239BB
00B	7/9/08	DJSM			REVISED AND RE-RELEASED TO TEAMCENTER REV HISTORY; TABULARIZED DIMS; REMOVED .86 AND .49 DIMS; REVISED .63 DIM TO INCLUDE TAPE; .73 WAS .74; REMOVED TAPE, APPLICATION, AND WARRANTY NOTES.	GB0239BB
3	7/18/00	JAD			DIMENSIONS, .63, .86, & .49 WERE CHANGED TO REF DIMENSIONS.	GB0239BB

TITLE
ACC62-A, ACC62-AT, ACC62-AV ADHESIVE CORD CLIP

CUSTOMER DRAWING

ITEM REVISION NAME: G03597BD/01

DATASET FILE NAME: G03597BD_DC_GB0239BB/01D

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.x ± .1 [2.54] .xxx ± .005 [.127]
.xx ± .01 [.25] ANGLES ± 5 °
THIRD ANGLE PROJECTION

MATERIAL: NYLON 6/6

DRAWING NUMBER: GB0239BB

DRAWN BY	DATE	CHK	SCALE	SIZE
JRL	9/11/92	JHAC	FULL	A

SHT 1 OF 1