
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. *	MATERIAL SUFFIX	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' REF.	'H' REF.	'I' REF.	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM2S6	NONE -0 -30 -69	#6 (M3) SCREW	0.630 [16.00]	0.425 [10.725]	0.275 [6.985]	0.215 [5.460]	0.060 [1.525]	0.155 [3.937]	0.090 [2.3]	0.286 [7.26]	0.151 [3.84]	MINIATURE INTERMEDIATE STANDARD	0.126 [57.0]
TM2S8	NONE -0 -30 -69	#8 (M4) SCREW							0.105 [2.7]	0.332 [8.43]	0.176 [4.47]		0.113 [51.5]



SECTION A - A

MATERIAL SUFFIX	MATERIAL
NONE	NYLON 6/6
-0	WEATHER RESISTANT NYLON
-30	HEAT STABILIZED NYLON
-69	FLAME RETARDANT NYLON

NOTES;

*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

*2. HOLE DIMENSIONS SHOULD ACCOMENDATE SPECIFIED RECOMMENDED FASTENER.

7 3. BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS STATED ON THE BAG.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
7	4/19/2021	RVU	RMHI	JADE	ADDED NOTE 3. UPDATED TEMPLATE DWG.	GAECN05805
6	1/13/2021	LGG			ADDED 120 MATERIAL BACK TO DRAWING.	GB0239EM

TITLE

TM2S TIE MOUNT

CUSTOMER DRAWING

ITEM REVISION NAME: G03597JV/01

DATASET FILE NAME: G03597JV_GB0239EM_07/01B

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .05 [1.3] .XXX ± .010 [.25]

.XX ± .02 [0.5] ANGLES ± 5 °

THIRD ANGLE PROJECTION

MATERIAL: SEE TABLE

DRAWING NUMBER: GB0239EM

DRAWN BY	DATE	CHK	SCALE	SIZE
AJV	12/17/96	JADE	NONE	A

SHT 1 OF 1

D10100DA/20