


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	*MATERIAL SUFFIX	"A" DIA.	"B"	MTG. SCREW	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIES
TMEH-S8	-0	0.18 (4.6)	1.62 (41.1)	#8 (M4)	1.04 (471.4)	I,S,H,EH
TMEH-S10	-0	0.20 (5.1)	1.62 (41.1)	#10 (M5)	1.03 (467.4)	I,S,H,EH
	-100 -109		1.65 (41.9)			
TMEH-S25	-0	0.26 (6.6)	1.62 (41.1)	1/4" (M6)	1.01 (458.0)	I,S,H,EH





*MATERIAL SUFFIX	MATERIAL
-0	WEATHER RESISTANT NYLON
-100	WEATHER RESISTANT POLYPROPYLENE
-109	POLYPROPYLENE

NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. CABLE TIE CROSS SECTION CODE: I=INTERMEDIATE,S=STANDARD H=HEAVY DUTY,EH=EXTRA HEAVY.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597JX_DC/03A - GB0239EL r03A

REV	DATE	BY	CHK	DESCRIPTION	ECN - R		APP		
03A	05-25-25	BDK	JADE	ADDED WELD LINE NOTATION TO TOP VIEW	011256	00	DJSL		
2	10/28/03	MSAD		ADDED SEPERATE TMEH-S10 ROW FOR -100 AND -109 PARTS, 0.50 (12.7) DIA WAS .52 (13.2), 'B' WAS 1.65 (41.9) FOR -0 PARTS, 0.72 (18.3) WAS .74 (18.8) 1.04 (26.4) WAS 1.05 (26.7)	GB0239EL	2			
1	7/24/01	LGG		ADDED REF & UPDATED	GB0239EL	1			
R	12/13/96	AJV		INITIAL RELEASE	GB0239EL	R			

PANDUIT CORP. TINLEY PARK, ILLINOIS

TMEH-XX TIE MOUNT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]
(.XX) ±0.02 [0.5] ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY AJV
DATE 12/13/96
CHK'D
MAT'L: SEE TABLE
SCALE NONE
DRAWING NO. GB0239EL
DWG A SIZE