


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	MIN. LOOP * TENSILE lbs. (N)	CROSS SECTION
	MIN. in (mm)	MAX. in (mm)							
HLT2I	.25 (6.4)	1.91 (48.5)	.100 (2.5) MAX	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	40 (178)	INTERMEDIATE
HLT3I		3.18 (80.6)					12.0 (305)		

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- * 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 3) A MATERIAL SLUG MAY BE PRESENT AFTER MANUFACTURING. THE SLUG MAY REMAIN IN THE SLOT OR BE ON THE TIES

									CAD FILENAME/LAYERS			SS_26938_08	
									PANDUIT CORP. TINLEY PARK, ILLINOIS				
									TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES				
09	9/15/20	JSP	DWW	D. ADDED MAX TO DIM A.		26938	9	ML					
08	1/7/20	JSP	DWW	C. ADDED NOTE #3.		26938	8	ML			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .030 (.XX) ± .125		
07	01/14/19	SAT	DWW	B. UPDATED MATERIAL. A. REMOVED APPROXIMATE WEIGHT COLUMN.		26938	7	ML			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
6	1/16/06	ERW		ADDED APPROX. WEIGHT PER 100 PIECES		26938	6			DRAWN BY KET	MAT'L:	SCALE NONE	
5	5/3/05	ERW	JVL	REMOVED OVAL SLOT DIMENSION TO BE CONSISTENT WITH OTHER CUSTOMER DRAWINGS		26938	5	JVL		DATE 11/28/94	BACK-TO-BACK HOOK AND LOOP HOOKS: POLYETHYLENE OR NYLON LOOPS: NYLON	DRAWING NO. SS-26938	DWG A
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP	CHK'D HVP	SIZE		