




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	MIN. LOOP TENSILE $l_{bs.}$ (N)	CROSS SECTION
	MIN. $\frac{in}{(mm)}$	MAX. $\frac{in}{(mm)}$									
HLC3S	2.0 (50.8)	3.0 (76.2)	.080 (2.0)	.750 (19.1)	.750 (19.1)	.183 (4.6)	1.10 (27.9)	12.0 (305)	.080 (2.0)	50 (222)	STANDARD
HLC5S	3.0 (76.2)	5.0 (127)	.080 (2.0)	.750 (19.1)	.750 (19.1)	.183 (4.6)	1.10 (27.9)	18.0 (457)	.080 (2.0)	50 (222)	STANDARD

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
- 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

							TITLE TAK-TY HOOK & LOOP CABLE TIES HLC SERIES CUSTOMER DRAWING						
							ITEM REVISION NAME SS-26935/AD						
							DATASET FILE NAME SS-26935/AD						
9	01-25-19	SAT	DWW	ML	C. REMOVED WEIGHT COLUMN.	SS-26935	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] . X ± .xxx ± .030 [.762] . XX ± .125 [3.175] ANGLES ±						
8	3/16/18	JSP	DWW	ML	B. ADDED TOLERNACE TO DIM. B.	SS-26935	THIRD ANGLE PROJECTION 						
7	5/20/14	RVU	DJW	KLN	A: .080 WAS .100. D: .183 WAS .156. G: .080 WAS .100. REMOVE .150 LEADER.	GAECN01997					MATERIAL: WOVEN NYLON HOOK/LOOP COLOR: BLACK		
6	3/31/06	ERW			ADDED "APPROXIMATE WEIGHT PER 100PCS" COLUMN.	26935					DRAWING NUMBER: SS-26935		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY KET	DATE 11/23/94	CHK HVP	SCALE NONE	SHT 1 OF 1	SIZE A	