




PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE ^{lbs.} (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. ⁱⁿ (mm)	MAX. ⁱⁿ (mm)									
UCT3S	.63 (16.0)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	50 (222)	STANDARD	.59 (267)
UCT5S	.63 (16.0)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.0 (457)	50 (222)	STANDARD	.81 (366)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
- MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS.

SS-27366-00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
ULTRA-CINCH HOOK & LOOP TIESUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .25 (.XXX) ± .030
(.XX) ± .125 ANGLES ±UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

8	1/13/12	CR-MBA	DJW	ALTERNATE MATERIAL ADDED; SPECIFIC COLOR REMOVED:	SS-27366	8	KLN			DRAWN BY JABO	MAT'L: WOVEN HOOK/LOOP NYLON OR POLYESTER	SCALE NONE	
7	4/12/06	FAB	DWW	ADDED PART WEIGHTS	27366	7	TGS			DATE 6/19/02		DRAWING NO.	DWG
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D DWW		SS-27366	A SIZE