




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	50 (222)	STANDARD	CURVED	.56 (254)
PLT4.5S	.06 (1.5)	4.50 (114)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	15.5 (394)	50 (222)	STANDARD	CURVED	.57 (257)
PLT5S	.06 (1.5)	5.00 (127)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	17.5 (445)	50 (222)	STANDARD	CURVED	.65 (293)
PLT6LH	.188 (4.8)	6.00 (152)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	21.9 (556)	120 (534)	LIGHT HEAVY	STRAIGHT	1.86 (845)
PLT7LH	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	120 (534)	LIGHT HEAVY	STRAIGHT	2.09 (950)
PLT8LH	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	27.6 (701)	120 (534)	LIGHT HEAVY	STRAIGHT	2.32 (1054)
PLT9LH	.188 (4.8)	9.00 (229)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	30.5 (775)	120 (534)	LIGHT HEAVY	STRAIGHT	2.56 (1161)
PLT10LH	.188 (4.8)	10.31 (262)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	34.3 (871)	120 (534)	LIGHT HEAVY	STRAIGHT	2.83 (1285)

NOTES:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE					
							PREMIUM CABLE TIES – PLT SERIES					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			W10001CC/28		
							DATASET FILE NAME			W10001CC_DC/28-SS-5540 SHT 3 r28A		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
							.x ± -					