


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


NO WARRANTY EXPRESSED, OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



PANDUIT PART NUMBER	BUNDLE DIA.		RECM. OPTIONAL FASTENER	WEIGHT lbs/100 (g)/PC'S
	MIN. IN. (MM)	MAX. IN. (MM)		
ARC.68-A	0.19 (4.8)	0.68 (17.3)	-----	0.42 (194)
ARC.68-S6			*6(M3) FHCS OR BHSC	0.38 (177)

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE AND
PART COLOR.
- 2) TO APPLY MOUNTS: a) REMOVE PROTECTIVE LINER;
b) PLACE IN DESIRED LOCATION; c) APPLY PRESSURE
TO TOP SURFACE OF MOUNT.



ADHESIVE TAPE--PRESSURE SENSITIVE FOAM 0.040(1.02) THICK
WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT
0.50 lb.(227g) MAX. WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

(E) G00239H0_PI_ARC.68_00



CORP. TINLEY PARK, ILLINOIS

ARC .68
ADJUSTABLE RELEASABLE CLAMP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
(.XX) ± 0.05 (1.3) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LGG

MAT'L:

DATE 5/12/02

POLYPROPYLENE

DRAWING NO.

GB0239H0

DWG
A
SIZE

1	7/30/01	JAD		REVISED FOR TEAR TAB ON EITHER SIDE	GB0237HO	1				
R	6/13/01	LGG		CHANGED DRAWING FROM SS-6770(RV 11)	GB0237HO	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

		CORP. TINLEY PARK, ILLINOIS	
ARC .68 ADJUSTABLE RELEASABLE CLAMP			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) $\pm 0.1(2.5)$ (.XXX) $\pm 0.020(.5)$ (.XX) $\pm 0.05(1.3)$ ANGLES $\pm 5^\circ$		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAIN BY LGG	MAT'L:	SCALE NONE	DWG A
DATE 6/13/01		DRAWING NO. GB0239H0	
CHK'D		SIZE 1/2	
POLYPROPYLENE			