


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Part Number	Width in. (mm)	Length ft. (m)	Thickness in. (mm)	Package per Roll	Description	Insulation Color	Weight oz. (gram)
ST14-075-60BK	.75 (19)	60 (18)	.007 (.18)	CELLO WRAP	General Purpose ST14 Black, .75" x 60'X .007"	BLACK	2.9 (82)
ST14-075-60BKX	.75 (19)	60 (18)	.007 (.18)	CELLO WRAP	General Purpose ST14 Black, 10 pcs, .75" x 60'X .007"	BLACK	29 (820)

TAPE
WIDTH



TAPE
THICKNESS



LISTED

Electrical Insulating Tape



CERTIFIED

- NOTES:
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 - ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 - MATERIAL: RUBBER ADHESIVE PRESSURE SENSITIVE VINYL TAPE.
 - TEMPERATURE RATING: -10 °C TO 80 °C.
 - DIELECTRICAL STRENGTH: 7000V.
 - FLAME RETARDANT.
 - MEETS UL-510 AND CSA C 22.2 NO. 197.
 - COMPLIANT TO CALIFORNIA PROP. 65

PART NUMBER		SEE TABLE		PACKAGING SPEC		PKG-516	
PRODUCT SPEC		PS-SH-002					
TITLE							
Stronghold Insulating Tape-General Purpose ST14 Tape							
CUSTOMER DRAWING							
ITEM REVISION NAME				00351EBS/00			
DATASET FILE NAME				00351EBS_DC/00			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				.x ± .1 [2.54] .xx ± .01 [.25] .xxx ± .005 [.127] ANGLES ± 1°			
THIRD ANGLE PROJECTION				MATERIAL: SEE NOTE3			
DRAWING NUMBER:				00351EBS_DC			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
JSUN	04/29/2019	ADAH	NONE			A	

00	04/29/2019	JSUN	ADAH	JHAC	INITIAL RELEASE	046173/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN