




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT3I	.06 (1.5)	3.00 (76)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	11.4 (290)	40 (178)	INTERMEDIATE	CURVED	.32 (145)
PLT4I	.06 (1.5)	4.00 (102)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	14.5 (368)	40 (178)	INTERMEDIATE	CURVED	.40 (181)
PLT1S	.06 (1.5)	1.00 (25)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	4.8 (122)	50 (222)	STANDARD	CURVED	.13 (58)
PLT1.5S	.06 (1.5)	1.50 (38)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	6.2 (157)	50 (222)	STANDARD	CURVED	.26 (118)
PLT2S	.06 (1.5)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	CURVED	.29 (132)
PLT2.5S	.06 (1.5)	2.50 (63.5)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	9.8 (249)	50 (222)	STANDARD	CURVED	.38 (173)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	CURVED	.45 (204)

NOTES:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE	
						PREMIUM CABLE TIES - PLT SERIES	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
						W10001CB/33	
						DATASET FILE NAME	
						W10001CB_DC/32 SS-5540 SH2_r33A	MATERIAL: NYLON 6.6
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .005 .xx ± .01 .xxx ± .020 [.51] ANGLES ± .005	
						THIRD ANGLE PROJECTION	
33A	10.02.24	BWG	JADE	DJSL	UPDATED TITLE BLOCK WITH ALTERNATE DESCRIPTION	005806/00	DRAWING NUMBER: SS-5540 SHEET 2
32	10/01/15	BWG	MPH	JADE	REVISED NOTES.	SS-5540/32	
31	8/13/13	BWG	KJM	RTFI	CORRECTED REV NO. REMOVED NOTE 1. SEE ECN FOR DETAILS.	SS-5540/30	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: CEW DATE: 12-27-84 CHK: HVP SCALE: NONE SHT 2 OF 4 SIZE: A