



The SKINDICHT® E-M is an incised sealing ring made of neoprene for SKINDICHT® cable glands. The rings can be cut out/break out for a various clamping range.

Technical features:

Material	CR (UV-resistant, oil-resistant)
Sizes	M12 up to M63
Temperature range	-20 °C up to +80 °C
Colour	Black





Article designation	Ø A [mm]	Ø d1 [mm]	Ø d2 [mm]	Ø d3 [mm]	Ø d4 [mm]	C [mm]	Article No.
E-M12	10,0	5,0	-	-	-	5,0	52100620
E-M16	13,8	3,0	6,0	9,0	-	5,5	52100621
E-M20	17,6	4,0	7,0	10,0	13,0	6,0	52100622
E-M25	22,6	8,5	11,5	14,5	17,5	7,5	52100623
E-M32	29,6	16,0	19,0	22,0	25,0	9,5	52100624
E-M40	37,6	23,0	26,0	29,0	32,0	12,0	52100625
E-M50	47,5	32,0	35,0	38,0	41,0	12,0	52100626
E-M63	60,3	41,0	44,0	47,0	50,0	14,0	52100627

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

We reserve all rights according to DIN ISO 16016.