

TOOL SET

62-PIECE ELECTRIC SCREWDRIVER TOOL SET

JOY-IT

SPECIAL FEATURES

- ✓ 60 bits included, made from high-quality S2 tool steel
- ✓ High-quality transport box for screwdrivers incl. bits
- ✓ 4 adjustable torque levels
- ✓ Rechargeable via USB-C
- ✓ Integrated, automatic illumination
- ✓ Rotating, magnetic bit storage



The 62-piece electric screwdriver tool set combines the highest material quality, innovative technology and a well thought-out design to offer you maximum precision, convenience and efficiency for every screw-driving task. The 60 carefully selected bits made from durable S2 tool steel guarantee outstanding stability and durability even under intensive use.

The ergonomic handle of the electric screwdriver sits comfortably in the hand, while the four adjustable torque levels ensure that you always apply the right amount of force, even with sensitive materials or particularly tight connections. The integrated, automatic illumination ensures optimum visibility, even in dark corners or confined spaces, so that you always have an overview.

For particularly high working speed and maximum maximum tidiness thanks to the rotating, magnetic bit It reliably holds all bits in place and enables quick, intuitive replacement without you having to search for the right insert for a long time.

At the same time, the robust and attractive transport box protects the screwdriver and all bits from dust, dirt and damage - ideal for flexible use in the workshop, garage or on the go. Convenient charging via the USB-C connection ensures that your tool set is always ready for use without you having to worry about special charging cables or complicated connections.

This 62-piece set is therefore far more than just a simple helper: it is an indispensable all-round package that offers you safety, precision and durability in every step of your work.

MAIN FEATURES	
Number of bits	60
Material	Bits: S2 - tool steel, bit storage: plastic Case: Aluminum
Battery	500 mAh LI-ION battery, rechargeable via USB-C
Torque	Electrical: 0.1 - 0.3 NM, Manual: 3 NM
Rotations	165 RPM
Illumination	Automatic lighting by 4 integrated LEDs

INCLUDED BITS	
	PH0000, PH000, PH00, PH0, PH1, PH2
	SL1.0, SL1.5, SL2.0, SL2.5, SL3.0, SL3.5, SL4.0
	T2, T3, T4
	T5H, T6H, T7H, T8H, T9H, T10H, T15H, T20H
	H0.7, H0.9, H1.3, H1.5, H2.0, H2.5, H3.0, H3.5, H4.0
	Y0.6, Y1.0, Y1.5, Y2.0, Y2.5, Y3.0, Y1
	PZ000, PZ00, PZ0, PZ1, PZ2
	SQ0, SQ1, SQ2
	SIM
	U2.0, U2.6, U3.0
	2.0, 2.5
	2.0, 2.3, 3.0
	P2, P5, P6

ADDITIONAL INFORMATION	
Dimensions	Storage box: 183 x 41 mm, screwdriver: 160 x 18 mm
Weight	395 g
Article No.	WE-0004
Items shipped	Electric screwdriver, bit holder, 60 bits, USB-C charging cable
EAN	4250236828978
Customs tariff number	82079030

