

Kryonaut extreme

High Performance Cooling Solutions – Made in Germany

Kryonaut Extreme is a high-performance thermal compound based on our proven Kryonaut thermal compound. Above all, the improved low-temperature load capacity sets Kryonaut Extreme apart from other heat-conducting pastes. The smallest particle size and layer thickness enable maximum thermal conductivity, which forms the basis for the best temperatures during extreme overclocking.

Additional, electrically non-conductive nano-aluminum oxide particles make Kryonaut Extreme an extremely high-performance thermal compound. The smallest possible particle size for optimal application allows for better filling of microscopic imperfections and thus enables better thermal conductivity. Developed over several years in cooperation with renowned engineers and pro overclockers, Kryonaut Extreme is the new top product especially for extreme overclocking - both in the low temperature range, e.g. with liquid nitrogen, and at ambient temperature, e.g. with water cooling systems.

Please note

The data in this technical data sheet are based on our current knowledge and experience. Due to the large amount of possible factors, this should not be construed as to release the users from doing their own tests and screening. No legally binding assurance of specific properties or applicability for a concrete purpose should be derived from these data. Please consider contacting us for further detail. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed.



Short informations

- Especially for overclocking
- No hardening
- Not electrically conductive

Scope of delivery 9ml

- 1x Kryonaut extreme
- 3x TG Spatula

Scope of delivery 2g

- 1x Kryonaut extreme
- 2x Applicator

Trademark Information

Thermal Grizzly is a registered trademark.

Technical data

Unit:	Value/description:
Colour:	Pink
Electrical conductivity** :	0 pS/m
Viscosity:	130–180 Pas
Density:	3,76g/cm ³
Temperature:	-250 °C / +350 °C
Typical application:	CPUs, GPUs, Notebooks, ICs

Item number:	EAN-Code:	Contents:	Package size:	*Net weight:	*Gross weight:	PU:
TG-KE-002-R	4260711990052	2 g	19x10x1 cm	5 g	14 g	50 Pcs.
TG-KE-090-R	4260711990069	9 ml/33,84 g	10,5x8,5x4 cm	38 g	100 g	14 Pcs.

*Net weight is the total weight of an article excluding the weight of packaging and accessories. The gross weight refers to the total weight of the product including accessories and packaging. Slight weight deviations are possible due to production factors.

**according to DIN 51412-1

Thermal interface material – Paste 30x30 240 W

