

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC-15D FLEX CLAMP



Item no. 3500058

TECHNICAL DATA

Power supply.....	3x AAA 1.5V batteries
Display count.....	6000
Display refresh.....	approx. 2~3 times per second
Range.....	Automatic
Polarity display.....	Automatic
Overrange.....	"OL" displayed
Impact resistance.....	approx. 1m
Low battery indication.....	≤3.6V
Auto power off.....	approx. 15 mins of no activity
Operating temperature.....	0 to +40 °C
Storage temperature.....	-10 to + 50 °C
Relative humidity.....	≤75 % for 0 to +30 °C ≤50 % for 30 to +40 °C
Operating altitude.....	≤2000 m
Electromagnetic compatibility.....	EN61326-1: EN61326-2-2
Safety standard.....	EN 61010-1 CAT III 1000V / CAT IV 600V
Pollution degree.....	2
Weight.....	258.4 g (without battery)

PACKAGE CONTENTS

- Meter
- Test leads
- 3x 1.5 V AAA batteries

