



DATASHEET

Silicon wire box set, 1.27 mm², 5 coils x 5 m, Red, Black, Yellow, Blue, Green



Item No.:	Wire gauge	Conductor	Sectional Area/mm ²	OD/mm	Length rolls/m
3521254	16 AWG	252/0.08 TC	1.27	3.0 ±0.1	5
3521255	17 AWG	210/0.08 TC	1	2.7 ±0.1	5
3521256	18 AWG	150/0.08 TC	0.75	2.3 ±0.1	5
3521257	20 AWG	100/0.08 TC	0.5	1.8 ±0.1	5
3521258	22 AWG	60/0.08 TC	0.3	1.7 ±0.1	5
3521259	26 AWG	30/0.08 TC	0.15	1.5 ±0.1	10
3521260	28 AWG	16/0.08 TC	0.08	1.2 ±0.1	10
3521261	30 AWG	11/0.08 TC	0.055	0.8 ±0.1	20

Features

- Rated voltage: 300V DC/AC
- Insulation material: Silicone rubber
- Conductor material: Tinned copper
- Rated Temperature: -60 to +200 °C
- Rolls: 5
- Colour: Red, black, yellow, blue, green