




BU-1420701841
(CONN SMA JACK STR 50 OHM EDGE MNT)





(Dimensions in Inches)

- Impedance: 50 Ohms
- Frequency Range: 0-18G
- Working Voltage: 335V at Sea Level
- Dielectric Withstanding Voltage: 1000V Min at Sea Level
- Contact Resistance at Contact: < 3.0 milliohms
- Material:
 - Body: "1U" Gold plated Brass
 - Contact: "3U" Gold plated Beryllium Copper
 - Insulator: Teflon
- Meets or exceeds the applicable paragraph of Mil-C-39012
- Operating Temperature: -65°C (-85°F) to 150°C (302°F)
- RoHS 3 Compliant