

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision	Unit
1.	Supplier's name or trademark.	ARZOPA	
	Supplier's address.	THEMIS AR Unterstützung UG , Beedstrasse 54, In Dusseldorf, (40468), Deutschland, DE	
2.	Model identifier	E1	
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	E	
4.	On mode power demand in SDR	16,2	W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	n.a.	
6.	On mode power demand in HDR, if implemented	n.a.	W
7.	Off mode, power demand, if applicable	0,0	W
8.	Standby mode power demand, if applicable	0,4	W
9.	Networked standby mode power demand, if applicable	0,0	W
10.	Electronic display category	Monitor	
11.	Size ratio	16 : 9	
12.	Screen resolution	1 920 x 1 080	pixels
13.	Screen diagonal	40,6	cm
14.	Screen diagonal	16	inches
15.	Visible screen area	13,4	dm ²
16.	Panel technology used	LCD	
17.	Automatic Brightness Control (ABC) available	No	
18.	Voice recognition sensor available	No	
19.	Room presence sensor available	No	
20.	Image refresh frequency rate (default)	60	Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	1	Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	1	Years
23.	Minimum guaranteed product support	1	Years
	Minimum duration of the general guarantee offered by the supplier	1	Years
24.	Power supply type	External	
25.	External power supply (non standardized and included in the product box)		
	<i>i</i> AC/DC ADAPTER		

	<i>ii</i>	Input voltage	230	V
	<i>iii</i>	Output voltage	12,0	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 08/12/2025.



EPREL registration number: 2563633

<https://eprel.ec.europa.eu/qr/2563633>

Supplier: Donghuababa (Authorised representative)

Website:

Customer care service:

Name: THEMIS AR Unterstützung UG

Website:

Email: legal@themisar.com

Phone: +49-21173714852

Address:

Beedstrasse 54, In Dusseldorf, (40468), Deutschland
Germany