

Heat-Shrink-Tube Reels 2:1



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The standard version with a shrink ratio of 2:1 without internal adhesive is ideal for most applications.

Technical data: Material: PE • Shrink ratio: 2:1 • Shrink temperature (min.): 90 °C
Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... 125 °C
Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 s.) • Rated voltage: 600 V
Elongation break: min. 300% • Colors: Black, White, Transparent • Selling unit: Reel.

Item-No.	Description	Diameter	Wall thickness material	Diameter shrunk	Wall thickness shrunk	Content	EAN/GTIN
EG25CA001	Shrinking tube 2:1 black Ø 1 mm roll 200 m	1 mm	0.16 (±0.02) mm	0,5 mm	0.32 (±0.04) mm	200 m	4262511622980
EG25CA002	Shrinking tube 2:1 black Ø 2 mm roll 200 m	2 mm	0.18 (±0.02) mm	1 mm	0.36 (±0.04) mm	200 m	4262511622997
EG25CA003	Shrinking tube 2:1 black Ø 4 mm roll 100 m	4 mm	0.19 (±0.02) mm	2 mm	0.38 (±0.04) mm	200 m	4262511623000
EG25CA004	Shrinking tube 2:1 black Ø 6 mm roll 100 m	6 mm	0.21 (±0.02) mm	3 mm	0.42 (±0.04) mm	100 m	4262511623017
EG25CA005	Shrinking tube 2:1 black Ø 8 mm roll 100 m	8 mm	0.21 (±0.02) mm	4 mm	0.42 (±0.04) mm	100 m	4262511623024
EG25CA006	Shrinking tube 2:1 black Ø 10 mm roll 100 m	10 mm	0.22 (±0.02) mm	5 mm	0.44 (±0.04) mm	100 m	4262511623031
EG25CA007	Shrinking tube 2:1 black Ø 12 mm roll 100 m	12 mm	0.23 (±0.02) mm	6 mm	0.46 (±0.04) mm	100 m	4262511623048
EG25CA008	Shrinking tube 2:1 black Ø 14 mm roll 100 m	14 mm	0.23 (±0.02) mm	7 mm	0.46 (±0.04) mm	100 m	4262511623055
EG25CA009	Shrinking tube 2:1 black Ø 16 mm roll 50 m	16 mm	0.24 (±0.02) mm	8 mm	0.48 (±0.04) mm	100 m	4262511623062
EG25CA010	Shrinking tube 2:1 black Ø 18 mm roll 50 m	18 mm	0.24 (±0.02) mm	9 mm	0.48 (±0.04) mm	50 m	4262511623079
EG25CA011	Shrinking tube 2:1 black Ø 20 mm roll 50 m	20 mm	0.25 (±0.02) mm	10 mm	0.5 (±0.04) mm	50 m	4262511623086
EG25CA012	Shrinking tube 2:1 black Ø 25 mm roll 25 m	25 mm	0.27 (±0.03) mm	12,5 mm	0.54 (±0.06) mm	50 m	4262511623093
EG25CA013	Shrinking tube 2:1 black Ø 30 mm roll 25 m	30 mm	0.28 (±0.03) mm	15 mm	0.56 (±0.06) mm	25 m	4262511623109
EG25CA014	Shrinking tube 2:1 black Ø 35 mm roll 25 m	35 mm	0.29 (±0.03) mm	17,5 mm	0.58 (±0.06) mm	25 m	4262511623116
EG25CA015	Shrinking tube 2:1 black Ø 40 mm roll 25 m	40 mm	0.3 (±0.03) mm	20 mm	0.6 (±0.06) mm	25 m	4262511623123
EG25CA016	Shrinking tube 2:1 black Ø 50 mm roll 25 m	50 mm	0.33 (±0.03) mm	25 mm	0.66 (±0.06) mm	25 m	4262511623130
EG25CA017	Shrinking tube 2:1 black Ø 60 mm roll 25 m	60 mm	0.35 (±0.03) mm	30 mm	0.7 (±0.06) mm	25 m	4262511623147
EG25CA018	Shrinking tube 2:1 black Ø 70 mm roll 25 m	70 mm	0.38 (±0.03) mm	35 mm	0.76 (±0.06) mm	25 m	4262511623154
EG25CA019	Shrinking tube 2:1 black Ø 80 mm roll 25 m	80 mm	0.4 (±0.03) mm	40 mm	0.8 (±0.06) mm	25 m	4262511623161
EG25CA020	Shrinking tube 2:1 black Ø 90 mm roll 25 m	90 mm	0.45 (±0.03) mm	45 mm	0.9 (±0.06) mm	25 m	4262511623178
EG25CA021	Shrinking tube 2:1 black Ø 100 mm roll 200 m	100 mm	0.49 (±0.03) mm	50 mm	0.89 (±0.06) mm	25 m	4262511623185
EG25CA022	Shrinking tube 2:1 white Ø 1 mm roll 200 m	1 mm	0.16 (±0.02) mm	0,5 mm	0.32 (±0.04) mm	200 m	4262511623192
EG25CA023	Shrinking tube 2:1 white Ø 2 mm roll 200 m	2 mm	0.18 (±0.02) mm	1 mm	0.36 (±0.04) mm	200 m	4262511623208
EG25CA024	Shrinking tube 2:1 white Ø 4 mm roll 100 m	4 mm	0.19 (±0.02) mm	2 mm	0.38 (±0.04) mm	200 m	4262511623215
EG25CA025	Shrinking tube 2:1 white Ø 6 mm roll 100 m	6 mm	0.21 (±0.02) mm	3 mm	0.42 (±0.04) mm	100 m	4262511623222
EG25CA026	Shrinking tube 2:1 white Ø 8 mm roll 100 m	8 mm	0.21 (±0.02) mm	4 mm	0.42 (±0.04) mm	100 m	4262511623239
EG25CA027	Shrinking tube 2:1 white Ø 10 mm roll 100 m	10 mm	0.22 (±0.02) mm	5 mm	0.44 (±0.04) mm	100 m	4262511623246
EG25CA028	Shrinking tube 2:1 white Ø 12 mm roll 100 m	12 mm	0.23 (±0.02) mm	6 mm	0.46 (±0.04) mm	100 m	4262511623253
EG25CA029	Shrinking tube 2:1 white Ø 14 mm roll 100 m	14 mm	0.23 (±0.02) mm	7 mm	0.46 (±0.04) mm	100 m	4262511623260
EG25CA030	Shrinking tube 2:1 white Ø 16 mm roll 50 m	16 mm	0.24 (±0.02) mm	8 mm	0.48 (±0.04) mm	100 m	4262511623277
EG25CA031	Shrinking tube 2:1 white Ø 18 mm roll 50 m	18 mm	0.24 (±0.02) mm	9 mm	0.48 (±0.04) mm	50 m	4262511623284
EG25CA032	Shrinking tube 2:1 white Ø 20 mm roll 50 m	20 mm	0.25 (±0.02) mm	10 mm	0.5 (±0.04) mm	50 m	4262511623291
EG25CA033	Shrinking tube 2:1 white Ø 25 mm roll 25 m	25 mm	0.27 (±0.03) mm	12,5 mm	0.54 (±0.06) mm	50 m	4262511623307
EG25CA034	Shrinking tube 2:1 white Ø 30 mm roll 25 m	30 mm	0.28 (±0.03) mm	15 mm	0.56 (±0.06) mm	25 m	4262511623314
EG25CA035	Shrinking tube 2:1 white Ø 35 mm roll 25 m	35 mm	0.29 (±0.03) mm	17,5 mm	0.58 (±0.06) mm	25 m	4262511623321
EG25CA036	Shrinking tube 2:1 white Ø 40 mm roll 25 m	40 mm	0.3 (±0.03) mm	20 mm	0.6 (±0.06) mm	25 m	4262511623338



Item-No.	Description	Diameter	Wall thickness material	Diameter shrunked	Wall thickness shrunked	Content	EAN/GTIN
EG25CA037	Shrinking tube 2:1 white Ø 50 mm roll 25 m	50 mm	0.33 (±0.03) mm	25 mm	0.66 (±0.06) mm	25 m	4262511623345
EG25CA038	Shrinking tube 2:1 white Ø 60 mm roll 25 m	60 mm	0.35 (±0.03) mm	30 mm	0.7 (±0.06) mm	25 m	4262511623352
EG25CA039	Shrinking tube 2:1 white Ø 70 mm roll 25 m	70 mm	0.38 (±0.03) mm	35 mm	0.76 (±0.06) mm	25 m	4262511623369
EG25CA040	Shrinking tube 2:1 white Ø 80 mm roll 25 m	80 mm	0.4 (±0.03) mm	40 mm	0.8 (±0.06) mm	25 m	4262511623376
EG25CA041	Shrinking tube 2:1 white Ø 90 mm roll 25 m	90 mm	0.45 (±0.03) mm	45 mm	0.9 (±0.06) mm	25 m	4262511623383
EG25CA042	Shrinking tube 2:1 white Ø 100 mm roll 200 m	100 mm	0.49 (±0.03) mm	50 mm	0.89 (±0.06) mm	25 m	4262511623390
EG25CA043	Shrinking tube 2:1 Transparent Ø 1 mm roll 200 m	1 mm	0.16 (±0.02) mm	0,5 mm	0.32 (±0.04) mm	200 m	4262511623406
EG25CA044	Shrinking tube 2:1 Transparent Ø 2 mm roll 200 m	2 mm	0.18 (±0.02) mm	1 mm	0.36 (±0.04) mm	200 m	4262511623413
EG25CA045	Shrinking tube 2:1 Transparent Ø 4 mm roll 100 m	4 mm	0.19 (±0.02) mm	2 mm	0.38 (±0.04) mm	200 m	4262511623420
EG25CA046	Shrinking tube 2:1 Transparent Ø 6 mm roll 100 m	6 mm	0.21 (±0.02) mm	3 mm	0.42 (±0.04) mm	100 m	4262511623437
EG25CA047	Shrinking tube 2:1 Transparent Ø 8 mm roll 100 m	8 mm	0.21 (±0.02) mm	4 mm	0.42 (±0.04) mm	100 m	4262511623444
EG25CA048	Shrinking tube 2:1 Transparent Ø 10 mm roll 100 m	10 mm	0.22 (±0.02) mm	5 mm	0.44 (±0.04) mm	100 m	4262511623451
EG25CA049	Shrinking tube 2:1 Transparent Ø 12 mm roll 100 m	12 mm	0.23 (±0.02) mm	6 mm	0.46 (±0.04) mm	100 m	4262511623468
EG25CA050	Shrinking tube 2:1 Transparent Ø 14 mm roll 100 m	14 mm	0.23 (±0.02) mm	7 mm	0.46 (±0.04) mm	100 m	4262511623475
EG25CA051	Shrinking tube 2:1 Transparent Ø 16 mm roll 50 m	16 mm	0.24 (±0.02) mm	8 mm	0.48 (±0.04) mm	100 m	4262511623482
EG25CA052	Shrinking tube 2:1 Transparent Ø 18 mm roll 50 m	18 mm	0.24 (±0.02) mm	9 mm	0.48 (±0.04) mm	50 m	4262511623499
EG25CA053	Shrinking tube 2:1 Transparent Ø 20 mm roll 50 m	20 mm	0.25 (±0.02) mm	10 mm	0.5 (±0.04) mm	50 m	4262511623505
EG25CA054	Shrinking tube 2:1 Transparent Ø 25 mm roll 25 m	25 mm	0.27 (±0.03) mm	12,5 mm	0.54 (±0.06) mm	50 m	4262511623512
EG25CA055	Shrinking tube 2:1 Transparent Ø 30 mm roll 25 m	30 mm	0.28 (±0.03) mm	15 mm	0.56 (±0.06) mm	25 m	4262511623529
EG25CA056	Shrinking tube 2:1 Transparent Ø 35 mm roll 25 m	35 mm	0.29 (±0.03) mm	17,5 mm	0.58 (±0.06) mm	25 m	4262511623536
EG25CA057	Shrinking tube 2:1 Transparent Ø 40 mm roll 25 m	40 mm	0.3 (±0.03) mm	20 mm	0.6 (±0.06) mm	25 m	4262511623543
EG25CA058	Shrinking tube 2:1 Transparent Ø 50 mm roll 25 m	50 mm	0.33 (±0.03) mm	25 mm	0.66 (±0.06) mm	25 m	4262511623550
EG25CA059	Shrinking tube 2:1 Transparent Ø 60 mm roll 25 m	60 mm	0.35 (±0.03) mm	30 mm	0.7 (±0.06) mm	25 m	4262511623567
EG25CA060	Shrinking tube 2:1 Transparent Ø 70 mm roll 25 m	70 mm	0.38 (±0.03) mm	35 mm	0.76 (±0.06) mm	25 m	4262511623574
EG25CA061	Shrinking tube 2:1 Transparent Ø 80 mm roll 25 m	80 mm	0.4 (±0.03) mm	40 mm	0.8 (±0.06) mm	25 m	4262511623581
EG25CA062	Shrinking tube 2:1 Transparent Ø 90 mm roll 25 m	90 mm	0.45 (±0.03) mm	45 mm	0.9 (±0.06) mm	25 m	4262511623598
EG25CA063	Shrinking tube 2:1 Transparent Ø 100 mm roll 200 m	100 mm	0.49 (±0.03) mm	50 mm	0.89 (±0.06) mm	25 m	4262511623604