

Heat-Shrink-Tube Reels 3:1



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The version with inner glue and a shrink ratio of 3:1 is ideal for applications with high demands on the wrapping.

Technical data: Material: PE • Shrink ratio: 3:1 • Hot melt adhesive • Shrink temperature (min.): 80 °C
Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... +125 °C
Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 s.) • Rated voltage: 600 V
Elongation break: min. 200% • Color: Black • Colors: Black, White, Transparent • Selling unit: Reel.

Item-No.	Description	Diameter	Diameter shrinked	Content	EAN/GTIN
EG25CA064	Shrinking tube 3:1 black Ø 1.6 mm roll 200 m	1.6 mm	0.5 mm	200 m	4262511623611
EG25CA065	Shrinking tube 3:1 black Ø 2.4 mm roll 200 m	2.4 mm	0.8 mm	200 m	4262511623628
EG25CA066	Shrinking tube 3:1 black Ø 3.2 mm roll 100 m	3.2 mm	1.1 mm	200 m	4262511623635
EG25CA067	Shrinking tube 3:1 black Ø 4.8 mm roll 100 m	4.8 mm	1.6 mm	100 m	4262511623642
EG25CA068	Shrinking tube 3:1 black Ø 6.4 mm roll 100 m	6.4 mm	2.1 mm	100 m	4262511623659
EG25CA069	Shrinking tube 3:1 black Ø 7.9 mm roll 50 m	7.9 mm	2.6 mm	100 m	4262511623666
EG25CA070	Shrinking tube 3:1 black Ø 9.5 mm roll 50 m	9.5 mm	3.2 mm	50 m	4262511623673
EG25CA071	Shrinking tube 3:1 black Ø 12.7 mm roll 50 m	12.7 mm	4.2 mm	50 m	4262511623680
EG25CA072	Shrinking tube 3:1 black Ø 15.4 mm roll 50 m	15.4 mm	5.1 mm	50 m	4262511623697
EG25CA073	Shrinking tube 3:1 black Ø 19.1 mm roll 50 m	19.1 mm	6.4 mm	50 m	4262511623703
EG25CA074	Shrinking tube 3:1 black Ø 25.4 mm roll 25 m	25.4 mm	8.5 mm	50 m	4262511623710
EG25CA075	Shrinking tube 3:1 black Ø 30 mm roll 25 m	30 mm	10 mm	25 m	4262511623727
EG25CA076	Shrinking tube 3:1 black Ø 39 mm roll 25 m	39 mm	13 mm	25 m	4262511623734
EG25CA077	Shrinking tube 3:1 black Ø 50 mm roll 200 m	50 mm	16.7 mm	25 m	4262511623741
EG25CA078	Shrinking tube 3:1 white Ø 1.6 mm roll 200 m	1.6 mm	0.5 mm	200 m	4262511623758
EG25CA079	Shrinking tube 3:1 white Ø 2.4 mm roll 200 m	2.4 mm	0.8 mm	200 m	4262511623765
EG25CA080	Shrinking tube 3:1 white Ø 3.2 mm roll 100 m	3.2 mm	1.1 mm	200 m	4262511623772
EG25CA081	Shrinking tube 3:1 white Ø 4.8 mm roll 100 m	4.8 mm	1.6 mm	100 m	4262511623789
EG25CA082	Shrinking tube 3:1 white Ø 6.4 mm roll 100 m	6.4 mm	2.1 mm	100 m	4262511623796
EG25CA083	Shrinking tube 3:1 white Ø 7.9 mm roll 50 m	7.9 mm	2.6 mm	100 m	4262511623802
EG25CA084	Shrinking tube 3:1 white Ø 9.5 mm roll 50 m	9.5 mm	3.2 mm	50 m	4262511623819
EG25CA085	Shrinking tube 3:1 white Ø 12.7 mm roll 50 m	12.7 mm	4.2 mm	50 m	4262511623826
EG25CA086	Shrinking tube 3:1 white Ø 15.4 mm roll 50 m	15.4 mm	5.1 mm	50 m	4262511623833
EG25CA087	Shrinking tube 3:1 white Ø 19.1 mm roll 50 m	19.1 mm	6.4 mm	50 m	4262511623840



Item-No.	Description	Diameter	Diameter shrinked	Content	EAN/GTIN
EG25CA088	Shrinking tube 3:1 white Ø 25.4 mm roll 25 m	25.4 mm	8.5 mm	50 m	4262511623857
EG25CA089	Shrinking tube 3:1 white Ø 30 mm roll 25 m	30 mm	10 mm	25 m	4262511623864
EG25CA090	Shrinking tube 3:1 white Ø 39 mm roll 25 m	39 mm	13 mm	25 m	4262511623871
EG25CA091	Shrinking tube 3:1 white Ø 50 mm roll 200 m	50 mm	16.7 mm	25 m	4262511623888
EG25CA092	Shrinking tube 3:1 transparent Ø 1.6 mm roll 200 m	1.6 mm	0.5 mm	200 m	4262511623895
EG25CA093	Shrinking tube 3:1 transparent Ø 2.4 mm roll 200 m	2.4 mm	0.8 mm	200 m	4262511623901
EG25CA094	Shrinking tube 3:1 transparent Ø 3.2 mm roll 100 m	3.2 mm	1.1 mm	200 m	4262511623918
EG25CA095	Shrinking tube 3:1 transparent Ø 4.8 mm roll 100 m	4.8 mm	1.6 mm	100 m	4262511623925
EG25CA096	Shrinking tube 3:1 transparent Ø 6.4 mm roll 100 m	6.4 mm	2.1 mm	100 m	4262511623932
EG25CA097	Shrinking tube 3:1 transparent Ø 7.9 mm roll 50 m	7.9 mm	2.6 mm	100 m	4262511623949
EG25CA098	Shrinking tube 3:1 transparent Ø 9.5 mm roll 50 m	9.5 mm	3.2 mm	50 m	4262511623956
EG25CA099	Shrinking tube 3:1 transparent Ø 12.7 mm roll 50 m	12.7 mm	4.2 mm	50 m	4262511623963
EG25CA100	Shrinking tube 3:1 transparent Ø 15.4 mm roll 50 m	15.4 mm	5.1 mm	50 m	4262511623970
EG25CA101	Shrinking tube 3:1 transparent Ø 19.1 mm roll 50 m	19.1 mm	6.4 mm	50 m	4262511623987
EG25CA102	Shrinking tube 3:1 transparent Ø 25.4 mm roll 25 m	25.4 mm	8.5 mm	50 m	4262511623994
EG25CA103	Shrinking tube 3:1 transparent Ø 30 mm roll 25 m	30 mm	10 mm	25 m	4262511624007
EG25CA104	Shrinking tube 3:1 transparent Ø 39 mm roll 25 m	39 mm	13 mm	25 m	4262511624014
EG25CA105	Shrinking tube 3:1 transparent Ø 50 mm roll 200 m	50 mm	16.7 mm	25 m	4262511624021