

Hook-and-Loop Tape Roll



Hook-and-loop-tape without buckles for flexible use and cutting.
One side “Hook” / one side “Loop”.

Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: Black, White, Green, Yellow, Red, Blue • RoHS compliant, REACH compliant • 50 m per roll.



Part-No.	Description	Length	Width	Color	EAN/GTIN
EG25CA116	Hook-and-loop tape 50 m x 1 cm Black on Roll	50 m	1 cm	Black	4262511624137
EG25CA117	Hook-and-loop tape 50 m x 2 cm Black on Roll	50 m	2 cm	Black	4262511624144
EG25CA118	Hook-and-loop tape 50 m x 3 cm Black on Roll	50 m	3 cm	Black	4262511624151
EG25CA119	Hook-and-loop tape 50 m x 4 cm Black on Roll	50 m	4 cm	Black	4262511624168
EG25CA120	Hook-and-loop tape 50 m x 5 cm Black on Roll	50 m	5 cm	Black	4262511624175
EG25CA121	Hook-and-loop tape 50 m x 7,5 cm Black on Roll	50 m	7,5 cm	Black	4262511624182
EG25CA122	Hook-and-loop tape 50 m x 10 cm Black on Roll	50 m	10 cm	Black	4262511624199
EG25CA123	Hook-and-loop tape 50 m x 1 cm White on Roll	50 m	1 cm	White	4262511624205
EG25CA124	Hook-and-loop tape 50 m x 2 cm White on Roll	50 m	2 cm	White	4262511624212
EG25CA125	Hook-and-loop tape 50 m x 3 cm White on Roll	50 m	3 cm	White	4262511624229
EG25CA126	Hook-and-loop tape 50 m x 4 cm White on Roll	50 m	4 cm	White	4262511624236
EG25CA127	Hook-and-loop tape 50 m x 5 cm White on Roll	50 m	5 cm	White	4262511624243
EG25CA128	Hook-and-loop tape 50 m x 7,5 cm White on Roll	50 m	7,5 cm	White	4262511624250
EG25CA129	Hook-and-loop tape 50 m x 10 cm White on Roll	50 m	10 cm	White	4262511624267
EG25CA130	Hook-and-loop tape 50 m x 2 cm Green on Roll	50 m	2 cm	Green	4262511624274
EG25CA131	Hook-and-loop tape 50 m x 2 cm Red on Roll	50 m	2 cm	Red	4262511624281
EG25CA132	Hook-and-loop tape 50 m x 2 cm Yellow on Roll	50 m	2 cm	Yellow	4262511624298
EG25CA133	Hook-and-loop tape 50 m x 2 cm Blue on Roll	50 m	2 cm	Blue	4262511624304