



3D not to scale


Rating [A]	Color	Volt [V]	iMaXX Reference
1	Black	32	F7001 *
2	Grey	32	F7002
3	Violet	32	F7003
4	Pink	32	F7004
5	Tan	32	F7005
7.5	Brown	32	F7075
10	Red	32	F7010
15	Blue	32	F7015
20	Yellow	32	F7020
25	Natural	32	F7025
30	Green	32	F7030

* ISO 8820-3, 135% load not applicable for this rating

Fusing time DIN ISO 8820-3 [s]		
Load [%]	Minimum [s]	Maximum [s]
110 %	360,000	-
135 %	0.75	600
160 %	0.25	50
200 %	0.15	5
350 %	0.04	0.5
600 %	0.02	0.1

Revisions

Date	Type	Drawn	Date	Appr.
a 11/99	add 3 & 4A	Checked	02/99	GRH
b 06/01	DIN nomenclature	Standards	06/19	EB
c 05/03	OCR printing	Approved	06/19	AdH
d 06/07	re-drawn			
e 07/11	updated DIN to ISO	Scale 3 : 1		
f 03/12	updated dimensions	Projection	Tolerance ± 0.2 mm unless otherwise noted	
g 10/12	updated dimensions			
h 12/15	updated fuse markings			
i 06/19	added 1 & 2A			



Title	F7000 series, miniOTO blade fuse			
Drawing type	schematic			
Drawing number	F7000 drawing 1			
Sheet	1 of 1			
Layers	0 1 2	6	9	11