






Number	Description
1	Fuse element
2	Ceramic body
3	Transparent cover

Fusing time ISO 8820-6 [s]		
Load [%]	Minimum [s]	Maximum [s]
100 %	360,000	-
135 %	5	1,800
150 %	1	600
200 %	0.2	60
350 %	0.03	1
600 %	0.01	0.2

Note: mounting torque in test fixture
12 Nm ± 1

Rating	Volt	iMaXX Reference
[A]	[V]	
30	58	CF030
50	58	CF050
75	58	CF075
100	58	CF100
125	58	CF125
150	58	CF150
175	58	CF175
200	58	CF200
250	58	CF250
300	58	CF300

Note: Amperage rating and production date
(WWYY) stamped on metal part

Revisions			Drawn	Date	Appr.
a	10/14	Added CF030	Checked	06/12	GRH
b	06/15	Added trace code info	Standards	03/16	BE
c	03/16	Corrected ISO fusing time	Approved	03/16	AdH



Scale	not to scale	Title	CF series, cubeOTO fuse
Projection	Tolerance ± 0.2 mm unless otherwise noted	Drawing type	schematic
		Drawing number	CF drawing 1
		Sheet	1 of 1
		Layers / Sheet	0 1 2 6 9 11 Sheet 01