

1

2

3

4

A

A

B

B

C

C

D

D

E

E

F

F

10.65 +0/-0.1

25.05 ± 0.1

19.0

12.1 ± 0.1

5.00 ± 0.05

3D not to scale

12.6

5.9 ± 0.1

9.5 ± 0.1

Ø 5.65 ± 0.05

8.00 ± 0.25

25.30 ± 0.05

16.6 ± 0.1

13.35 ± 0.1

39.25

FLP7000 series miniOTO Low Profile blade fuse ref. table:


Rating [A]	Color	Volt [V]	iMaXX Reference
2	Gray	58	FLP7002
3	Violet	58	FLP7003
4	Pink	58	FLP7004
5	Tan	58	FLP7005
7.5	Brown	58	FLP7075
10	Red	58	FLP7010
15	Blue	58	FLP7015
20	Yellow	58	FLP7020
25	Natural	58	FLP7025
30	Green	58	FLP7030

iMaXX Reference	Description
HLP7325	FH pre assembled, miniOTO Low Profile fuse, 1.5mm ² black wire 135 mm each side (±5mm)
HLP7335	FH pre assembled, miniOTO Low Profile fuse, 2.5mm ² red wire 135 mm each side (±5mm)

Note: HLP7335 max. load 65% with > 120s duration applications

Revisions

Date	Type	Drawn	Date	Appr.
		Checked	08/11	GRH
		Standards	06/13	BE
		Approved	06/13	AdH
		Scale	Not to scale	
		Projection	Tolerance	
			± 0.2 mm unless otherwise noted	



Title	HLP7300 series, FLP fuse holder
Drawing type	schematic
Drawing number	HLP7300 drawing 2
Sheet	1 of 1
Layers / Sheet	0 1 2 6 9 11 Sheet 01