






Notes:

- 1: production year fuse holder body
- 2: production month fuse holder body
- 3: tool cavity number
- 4: production date fuse holder contacts

Materials:

Body material Ultramid A3X2G5, PA66 GF 25, black
 Tab contact CuFe 2P H130 (K65), DIN 17 670
 M5 square nut, Q195 steel, Zn plated, DIN 557 (2x)
 M5x8 PZ2 screw, galvanized steel grade 4.8, DIN 7985 (2x)



maxiOTO fuse reference table

iMaXX Ref.	Rating [A]	Color	Cable min. cross section
F9020	20	Yellow	1.5
F9025	25	Grey	2.0
F9030	30	Green	2.5
F9040	40	Orange	4.0
F9050	50	Red	6.0
F9060	60	Blue	10.0
F9070	70	Brown	10.0
F9080	80	Natural	16.0
F9100	100	Violet	16.0

ring terminal reference table


iMaXX Ref.	Description
CCX906QL	ring terminal DIN 5-6B, 6mm ²
CCX910QL	ring terminal DIN 5-10B, 10mm ²

cover reference table

iMaXX Ref.	Description
H9105	FH maxiOTO H9120 cover 1p

kit reference table

iMaXX Ref.	Description
H9125	Kit in bag, 1x H9120, 1x H9105, 2x CCX906QL, 2x CCX910QL

Revisions				Date	Appr.			
	Date	Type	Drawn	09/13	GRH			
a	06/08	Re-drawn	Checked	11/23	BE			
b	09/13	Re-drawn, new tooling	Standards					
c	09/13	Updated notes, materials and table	Approved	11/23	SS			
d	11/13	Updated dimensions						
e	04/17	Added ring terminal X-ref	Scale	not to scale		Title	H9120 series, maxiOTO blade fuse holder	
f	10/22	Added kit X-ref		Tolerance ± 0.2 mm unless otherwise noted		Drawing type	schematic	
g	11/23	Updated material square nut				Drawing number	H9120 drawing 1	
						Sheet	1 of 1	
						Layers / Sheet	0 1 2 6 8 9 Sheet 01	