




5RCC



Part No	Inductance	f _L	Tol	DCR	Temp. rise	Rated DC Current (A)		Dimensions					
	L (μH)	(MHz)	± (%)	(Ω)	Δ (°C)	I	I _{sat}	Ø d	Ø D1	A	Ø D max	F	F1
5RCC-2R5M-YY	2.5	1	20	0.005	< 15	6.0	18.0	1.00	5.0	20	7.3	11.0	6.1
5RCC-4R7M-YY	4.7	1	20	0.008	< 15	5.0	13.0	0.95	5.0	25	7.2	14.5	6.0
5RCC-7R0M-YY	7.0	1	20	0.017	< 15	3.0	11.0	0.71	5.0	20	6.7	15.3	5.7
5RCC-100M-YY	10.0	0.1	20	0.027	< 15	2.0	9.0	0.63	5.0	20	6.5	16.2	5.7
5RCC-120M-YY	12.0	0.1	20	0.024	< 15	2.5	8.5	0.63	5.0	25	6.5	14.9	5.7
5RCC-250M-YY	25.0	0.1	20	0.038	< 15	1.0	5.0	0.63	5.0	30	6.5	22.8	5.7

Core Material : Ferrite-Rod bar

Revision date : 30 Oct 2014

SPQ : Loose / Box 800 [-00]

Remarks : Customized Versions available on request.