	X1 PRO
Weight	191.5 grams
Video Resolution	4K@60/50/30/25/24fps 1080p@120/100/60/50/30/25/24fps Vertical Video: 2.7K@60/50/30/25/24fps 1080p@60/50/30/25/24fps
Video format	MP4 H.264 / H.265 (HEVC)
Slo-Motion	1080p@120/100fps
Image resolution	12MP
Image format	JPEG
Max Flight Time	16 minutes
FOV (Field of View)	104°
CMOS	1/2
Aperture	f/2.8
Video Stabilization	SmoothCapture 2.0 Two-axis gimbal + EIS
Active Collision Detection	Rear active collision detection Proximity sensors
Max height	120 m Subject to local regulations
OmniTerrain	Available
Max Auto-Follow Speed	42 km/h
Instantaneous Tracking Speed	60 km/h
Max Flight Time	16 minutes
Max Takeoff Altitude	5500 m
Wind Resistance	Level 5 (10.7 m/s)
Internal Storage	32 GB storage, supports MicroSD cards up to 1 TB
Flight modes	10+modes: Hover; Zoom out; Follow; Orbit; Bird's eye; Manual Control; Snapshot; Dolly track; Side track; Smart control; Cycling Mode; Ski Mode; Dolly Zoom; Indoor Follow, etc.

HOVERAir X1
PRO

The X1 PRO is a powerful, compact flying action camera that can capture all your favorite shots at 4K 60fps. It delivers ultimate flight performance with smooth stabilization, various automated flight modes, and enhanced follow functions for capturing your best action shots. Designed for easy use, it features a pocket-sized foldable design, 3-second palm takeoff, OmniTerrain capability, and rear collision detection for safe, stable flights in diverse conditions.



	X1 PROMAX
Weight	192.5 grams
Video Resolution	8K@30/25/24fps 4K@120/100/60/50/30/25/24fps 1080p@120/100/60/50/30/25/24fps HDR (10-bit HLG): 4K@60/50/30/25/24fps 1080p@60/50/30/25/24fps Vertical Video: 4K@30fps 2.7K@60/50/30/25/24fps (HDR support) 1080p@60/50/30/25/24fps (HDR support)
Video format	MP4 H.264 / H.265 (HEVC)
Slo-Motion	4K@120/100fps 1080p@120/100fps
Image resolution	12MP; 48MP
Image format	JPEG DNG (through future OTA update)
Max Flight Time	16 minutes
FOV (Field of View)	107°
CMOS	1/1.3
Aperture	f/2.55
Video Stabilization	SmoothCapture 2.0 Two-axis gimbal + EIS
Active Collision Detection	Vision-based rear active collision detection Vision and Proximity sensors
Max height	120 m Subject to local regulations
OmniTerrain	Available
Max Auto-Follow Speed	42 km/h
Instantaneous Tracking Speed	60 km/h
Max Flight Time	16 minutes
Max Takeoff Altitude	5500 m
Wind Resistance	Level 5 (10.7 m/s)
Internal Storage	64 GB storage, supports MicroSD cards up to 1 TB
Flight modes	10+modes: Hover; Zoom out; Follow; Orbit; Bird's eye; Manual Control; Snapshot; Dolly track; Side track; Smart control; Cycling Mode; Ski Mode; Dolly Zoom; Indoor Follow, etc.

HOVERAir X1

— PRO MAX —

The X1 PROMAX is the world's first 8K flying action camera, capturing stunning visuals in 8K at 30fps. Its compact, foldable design makes it easy to carry, while the simple palm takeoff, OmniTerrain adaptability, and collision detection ensure safe, seamless operation. Equipped with premium stabilization, the X1 PROMAX delivers exceptional clarity and performance in all conditions, perfect for capturing breathtaking shots wherever adventure takes you.

