

2150 : PC 42 PC 50 Plastic Pipe-Cutter



The + product :

Cutting load reduced by 20%:

The PTFE (polytetrafluorethylene) Teflon coating facilitates blade sliding. On average, the cutting load is reduced by 20% versus with a blade with a typical coating.

Fast cutting:

The patented double ratchet mechanism ensures easy and fast cutting. Blade secured during cutting.

4-in-1 tool:

Plastic pipe-cutter, chamferer, wire-cutter and trunking-cutter.

Description



The extremely low friction ration of the PTFE (polytetrafluorethylene) Teflon coating facilitates blade sliding. Cutting load reduced by 20%*. (*- 20% on average on different types of tubes compared to a regular coating).

Material cut: PVC, PP, PE, PER, PEX, ABS, PEHD, CPVC, PPR, PB, multilayer.

Cutting accuracy: the V-shaped blade enables easy, perpendicular cutting.

Practical: quick, tool-free blade change.

Soft Touch ® handle: non-slip for perfect control.

The shape of the upper arm perfectly guides the blade during cutting.

Integrated wire-cutter: max Ø: 12 mm, max cross section: 4G2.5 mm².

Integrated electric trunking cutter: maxi 25 x 12.5 mm (PC 42); max 32 x 12.5 mm (PC 50).

Chamfer angle: 15°.

References

SKU	A mm	A " OD	H mm	L mm	kg
215042	42	1.5/8	112	238	0,525

Sku	A mm	A " OD	H mm	L mm	kg
215050	50	2	112	248	0,545

