

2906 : Professional pipe cleaner VAL 26



The + product :

Flexible and strong cleaning cables.

Handy and light.

For use by hand or with a power drill (not supplied).

Description

Manual cable pipe cleaner for piping Ø25-75mm, maximum cable length 10m.

Supplied with cleaning cable Ø 7 mm, length 7.5 m, for piping Ø 25-50 mm :

- **Highly flexible** for **fast advance** in the piping, even in narrow pipe curves and elbows.
- Jointed auger for **easy passage in the elbows**.
- **High strength**, special high grade steel, **with steel core**.

Handy and light, **only 2.7kg** cable included.

Used manually for easy obstructions easy to remove.

Used with power drill (not supplied) **for tough obstructions:**

- Crank removable in a few seconds **without tools**.
- Hew adapter at the centre of the drum.
- Ergonomic Soft Touch® grip for **excellent control in rotation**.

Adjustable anti-ejection system: **prevents untimely cable exit and loss** inside the piping.

Plastic **anti-shock** and **anti-corrosion** drum with large openings for better viewing of the cable and faster drying after cleaning.

Chuck Ø 13 mm to tighten cleaning pipes of different diameters.

Optional capacities with cables Ø 10 mm / length 7.5 m and Ø 8 mm / length 10 m.



More Information

Tips	After each intervention: clean the cable and protect it against rust with pipe cleaner oil reference 290400.
Supplied with	Supplied with a pair of gloves.

References

Sku	Pipe Ø mm	Reach m	kg
290640	25 to 50	7,50	3,350

