



Field-wireable, M12, female, straight, 3+PE, S-coded, screw-/clamp contact, 630V 12A




Product data

Item description	PS-WAKC4K
Item-No.	8063400
Customs tariff-No.	85366990
Step-File	PS-WAKC4K.stp
EAN	4047106149192

Technical data

Connector	female, straight, M12
Number of pins	3+PE
Coding	S
Rated voltage	630V _{AC}
Current load per pin (at 40°C)	12A
Insulation resistance	≥10 ⁹ Ω
Resistance	≤ 3mΩ
Ambient temperature product	-40°C...+85°C
Contact material	Metal, CuZn, gold-plated
Contact-carrier material	Plastic, PA, BK
Grip body material	Plastic, PA, BK
Connecting cross-section	max. 1.50 mm ²
Cable outlet	8...10 mm
Connecting type	Screw-/clamp contact
Standards	IEC 61076-2-111
Degree of protection (mounted)	IP67
Mechanical life-cycle	>100 mating cycles
Degree of pollution	3
Style	straight

Manual



Classification

eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102
eCl@ss 9.0	27440102
ETIM 5.0	EC002635
ETIM 6.0	EC002635

Link to product

<https://www.escha.net/en/products/standard/field-wireable-connectors/8063400>