


Y-splitter, M8, male, straight, 3 poles, M8, female, straight, 3 poles, M8, female, straight, 3 poles









Product data	
Item description	MB-SSP3-2SKP3-2xAND
Item-No.	8083105
Customs tariff-No.	85366990
Step-File	MB-SSP3-2SKP3.stp
EAN	4047106254971

Technical data	Exit 0	Exit 1	Exit 2
Connector	male, M8	female, M8	female, M8
Contact material	Metal, CuZn, gold-plated	Metal, CuZn, gold-plated	Metal, CuZn, gold-plated
Contact-carrier material	Plastic, TPU, BK	Plastic, TPU, BK	Plastic, TPU, BK
Coupling nut material	Metal, CuZn, nickel-plated	Metal, CuZn, nickel-plated	Metal, CuZn, nickel-plated
Rated voltage	60V	60V	60V
Number of pins	3	3	3
Current load (at 40°C)	4A	4A	4A

Insulation resistance	≥10^8Ω
Ambient temperature product	-30°C...+90°C
Circuit logic	2x passive AND
Grip body material	Plastic, TPU, BU
Sealing (female) material	FPM/FKM
Mechanical life-cycle	>100 mating cycles
Standards	IEC 61076-2-104
Degree of protection (mounted)	IP65, IP67, IP68
Degree of pollution	3

Classification	
eCl@ss 6.0	27279201
eCl@ss 7.0	27279201
eCl@ss 8.0	27279201
eCl@ss 9.0	27440106
ETIM 5.0	EC002062
ETIM 6.0	EC002925

Link to product

https://www.escha.net/en/products/standard/t-splitters-y-splitters/8083105