

							
Part number (color grey)	DN-97609	DN-97610	DN-97614	DN-19 TRAY-2-55		DN-10 TRAY-1	DN-10-TRAY-2
Part number (color black)	DN-19 TRAY-1-SW	DN-19 TRAY-2-SW	DN-19 TRAY-1-400-SW	DN-19 TRAY-2-55-SW	DN-19 TRAY1-1000-ECB	DN-10-TRAY-1-B	DN-10-TRAY-2-B
Suitable cabinet type	19 inch	19 inch	19 inch	19 inch	19 inch	10 inch	10 inch
Suitable cabinet depth	all	≥ 450 mm	≥ 600 mm	≥ 800 mm	≥ 1000 mm	all	all
Dimensions (H x W x D)	45 x 483 x 250 mm	88 x 482 x 349 mm	44 x 482 x 399 mm	88 x 482 x 549 mm	44 x 486 x 770 mm	44 x 254 x 150 mm	44 x 254 x 200 mm
Height units (U)	1U	2U	1U	2U	1U	1U	1U
Load capacity	15 kg	25 kg	15 kg	25 kg	50 kg	25 kg	25 kg
Mounting type	Fixed	Fixed	Fixed	Fixed	Fixed	Fixed	Fixed
Fixing on 19"/10" profile rails	2-point fixing	2-point fixing	2-point fixing	2-point fixing	4-point fixing	2-point fixing	2-point fixing