



(Intenso)[®]
for everyday life

POWER BANK MC10000 I 20 W

Mobile Charger with integrated USB-C cable

(Intenso)[®]
for everyday life

QUALITY AUDIT
Tested in Germany ✓

Technical detail

Battery:	10000 mAh
Colour:	Grey / black
Battery type:	Li-polymer battery
Output:	<u>USB-C / Cable Out</u> Normal: 5.0 V/DC 3.0 A Power Delivery: 5.0 V/DC 3.0 A, 9.0 V/DC 2.22 A, 12.0 V/DC 1.67 A (max. 20.0 W) PPS: 5.0-11.0 V 2.0 A
Input:	<u>USB-C / Cable In</u> Normal: 5.0 V/DC 3.0 A Power Delivery: 5.0 V/DC 3.0 A, 9.0 V/DC 2.0 A, 12.0 V/DC 1.5 A (max 18.0 W)
Display:	4 status LEDs
Characteristics:	integrated USB-C cable, additional USB-C port, magnetic back for easy attachment to your smartphone, cable-based charging (up to 2,5x faster than wireless charging), overvoltage protection, discharge protection, overcharge protection, short circuit fuse
Accessories:	Self-adhesive metal ring for attachment to non-magnetic phone cases
Dimensions:	102 x 68 x 20 mm
Packaging unit:	2 pcs

Product data

Battery + Colour	Art. No.	EAN
10000 mAh	7340034	4 034303 037612

