



PRODUCT SPEC SHEET

SKU 9891-5

Model:VT-4435-5

EAN:3800170228795

VT-4435 30W LED FLOODLIGHT 6500K BLACK BODY GREY GLASS 185LM/W 5YRS WTY



IP65
STANDARD

05
YEAR
WARRANTY

- High quality LED SMD chip and high power driver
- Comparing with traditional halogen floodlights it can save upto 85% Energy
- Product designed with high lumen efficiency of 185 LM/W
- Constant current Integrated IC driver - Built in driver - no external power supply required
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in < 1s
Model:	VT-4435-5
Color Temperature:	6500K
CRI:	>70
Watts:	30
Lumens:	5550
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	White
Body Type:	Aluminium
Dimension:	164.5x34x153mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD

LISTING DETAILS

SKU:	9891-5
Model:	VT-4435-5
EAN:	3800170228795
Commodity Code:	9405429000

PACKAGING

Gross Weight (Kgs):	0.53
Unit CBM:	0.0015
Dimension:	164.5x34x153mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	169
Width (Box) mm:	39

Beam Angle:	115°
Energy Rating Label:	B (2021)
Energy Saving:	85 Energy
IP Rating:	IP65
IK Rating:	IK06
Long Life:	25,000 Hours
lumens per watt:	185
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Height (Box) mm:170