



PRODUCT SPEC SHEET

SKU 9893-5

Model:VT-4456-5

EAN:3800170227729

VT-4456 50W LED FLOODLIGHT 6500K BLACK BODY GREY GLASS 185LM/W



IP65
STANDARD

05
YEAR
WARRANTY

- Product designed with high lumen efficiency of 185 LM/W
- High quality LED SMD chip and high power driver
- IP65 ingress protection
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in < 1s
Model:	VT-4456-5
Color Temperature:	6500K
CRI:	>70
Watts:	50
Lumens:	9250
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	White
Body Type:	Aluminium
Dimension:	183.5x34x169mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD

LISTING DETAILS

SKU:	9893-5
Model:	VT-4456-5
EAN:	3800170227729
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	0.62
Unit CBM:	0.0019
Dimension:	183.5x34x169mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	190
Width (Box) mm:	39

Beam Angle:	115°
Energy Rating Label:	B (2021)
Energy Saving:	85 Energy
IP Rating:	IP65
IK Rating:	IK05
Long Life:	25,000 Hours
lumens per watt:	185
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Height (Box) mm:174