



PRODUCT SPEC SHEET

SKU 9896-5

Model:VT-44205-5

EAN:3800170227736

VT-44205 200W LED FLOODLIGHT 4000K BLACK BODY GREY GLASS 185LM/W



IP65
STANDARD

05
YEAR
WARRANTY

- Product designed with high lumen efficiency of 185 LM/W
- High quality LED SMD chip and high power driver
- IP65 ingress protection
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in < 1s
Model:	VT-44205-5
Color Temperature:	4000K
CRI:	>70
Watts:	200
Lumens:	37000
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	402.5x44x349.5mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD

LISTING DETAILS

SKU:	9896-5
Model:	VT-44205-5
EAN:	3800170227736
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	2.98
Unit CBM:	0.01128
Dimension:	402.5x44x349.5mm

MASTER BOX PACKAGING

Box Qty:	2
Qty Per Pallet:	
Length (Box) mm:	411
Width (Box) mm:	52

Beam Angle: 115°

Energy Rating Label: B (2021)

Wire Length: 1m

Energy Saving: 85 Energy

IP Rating: IP65

IK Rating: IK05

Long Life: 25,000 Hours

lumens per watt: 185

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

Height (Box) mm: 345