



PRODUCT SPEC SHEET

SKU 23838

Model:VT-4909-FC-S

EAN:3800170228870

VT-4909-FC 10W LED FAST CONNECTOR FLOODLIGHT PIR SENSOR 3000K BLACK BODY 120LM/W



IP65
STANDARD

02 YEAR
WARRANTY

Super Bright
120
LUMENS/W

- High quality Slim series Floodlight with PIR Sensor and Fast Connector
- Designed with high efficiency SMD Chips
- In-built junction box for direct plugin
- Powerful LED light source with high lumen efficiency of 120 LM/W
- 3-8m (Radius) Detection Distance
- Built Strong and durable with Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more

TECHNICAL INFORMATION

Dimmable:	No
Time Delay:	Min 7sec+2sec Max 7min+2min
Detection Range:	120°±20°
Instant Start:	0-100% in <1s
Model:	VT-4909-FC-S
Color Temperature:	3000K
Detection Distance:	3-8m (Radius)
CRI:	>70
Watts:	10
Lumens:	1200
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Black
Color for Web:	Warm White

LISTING DETAILS

SKU:	23838
Model:	VT-4909-FC-S
EAN:	3800170228870
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	0.43
Unit CBM:	0.00238
Dimension:	152.5x89.1x182.8mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	

Body Type:	Aluminium
Dimension:	152.5x89.1x182.8mm
Operation Temperature:	-20°C to +45°C
PF:	>0.7
LED Chip Type:	SMD
Beam Angle:	120°
Energy Rating Label:	E (2021)
Sensor Type:	PIR
Energy Saving:	85 Energy
IP Rating:	IP65
Long Life:	25,000 Hours
lumens per watt:	120

Length (Box) mm:	156
Width (Box) mm:	72
Height (Box) mm:	172