






Model No.: **GPCR123A**

Description	: Lithium Battery, CR123A
Chemical System	: Lithium Manganese Dioxide
Nominal Voltage	: 3.0 Volts
Nominal Capacity	: 1500mAh (Discharge at 10mA to 2.0V at 23°C)
Dimensions	: Ø17 mm x 34.5 mm
Terminals	: Flat, Recessed Negative Terminal
Jacket	: PVC Resin Label
Shelf Life	: Up to 10 years
Average Weight	: App. 16g
Application	: Smoke Detector, Sensors, Home Security Products, Medical Equipment
Operating Temperature	: -40°C to 60°C

Cross References:

Eveready	Duracell
EL 123AP	DL 123A



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.