

Datasheet | Air fryer 8L food

Brand: Gastronoma | Article number: 18290010 | Product EAN number: 8711902085881

Product specifications

Colour	RVS
Convection / Hot air	Yes
Cool-touch handles	Yes
Display	Yes
Grill function	No
Inner light	No
Mains adapter or power supply cable usage for 1	Main product
Material	Plastic
	Stainless Steel
Maximal temperature	200 °C
Maximum power consumption	1800 W
Maximum temperature	200 °C
Minimal temperature	80 °C
Non-slip feet	Yes
Non-stick coating	Yes, ceramic
Number of products in package	1 pcs
Oven capacity	8.0000 l
Oven type	Hot air fryer
Power plug	Type F (CEE 7/7)
Power source type	Mains Powered
Recipees included	No
Rotisserie / spit	No
Scratch and cut resistant	No
SmartLife	No
Suitable for snacks	Yes
Temperature indicator	Yes
Temperature range	80 - 200 °C
Temperature setting	Yes
Timer sda material	Yes
Total volume	8 l
Touch control	Yes
Volume	8 l
Warning signal	Yes

Packaging information

Brand	Gastronoma
Order code	18290010
EAN single product:	8711902085881
EAN Inner carton:	
EAN Outer carton:	
Packaging	Giftbox
Package contents	Cake tin
	Pizza pan

