

Polyester Braided Sleeving With Hook & Loop Closure



This cable bundling sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. The fabric consists of polyester mesh with PA hook-and-loop fasteners and is characterized by good heat resistance, noise reduction, abrasion resistance, dust resistance, easy and convenient handling, and reusability. It is closed using a hook-and-loop surface, allowing for easy installation also afterwards. The products are widely used for finishing and protecting or organizing cable harnesses, tidying up office spaces, electrical installations, and other applications.

To prevent fraying, the sleeve should be cut with a hot cutting tool!

Technical data: Material: polyester braid / polyamide hook-and-loop • Temperature range: -60 ... 125 °C • Melting temperature: 230 °C (±10°C) • Color: black • RoHS compliant, REACH compliant • Flammability class based on VW-1.

Part-No.	Description	Ø	Flat width	Color	Roll content	EAN/GTIN
25CA753	Hook & Loop Braided Sleeving ø 20 mm	20 mm	80 mm	Black	25 m	4262511625394
25CA754	Hook & Loop Braided Sleeving ø 25 mm	25 mm	95 mm	Black	25 m	4262511625400
25CA755	Hook & Loop Braided Sleeving ø 30 mm	30 mm	115 mm	Black	25 m	4262511625417
25CA756	Hook & Loop Braided Sleeving ø 35 mm	35 mm	130 mm	Black	25 m	4262511625424
25CA757	Hook & Loop Braided Sleeving ø 40 mm	40 mm	146 mm	Black	25 m	4262511625431
25CA758	Hook & Loop Braided Sleeving ø 45 mm	45 mm	162 mm	Black	25 m	4262511625448
25CA759	Hook & Loop Braided Sleeving ø 50 mm	50 mm	178 mm	Black	25 m	4262511625455
25CA760	Hook & Loop Braided Sleeving ø 70 mm	70 mm	240 mm	Black	25 m	4262511625462