

DATASHEET

Pneumatic Quick Couple, German Type, Female thread

Dimension drawing



Item No.	Model no.	L	ØD	L1	SW	FT
3594018	TC-TE7-2PF	35.5	11.9	16.3	19.0	1/4" BSP
3594019	TC-TE7-3PF	36.7	11.9	16.3	19.0	3/8" BSP
3594020	TC-TE7-4PF	39.8	11.9	19.2	23.9	1/2" BSP

Measurements for L, ØD, L1 are in mm, SW and FT are non-metric

Technical data

Working pressureMax. 10 bar
 Temperature range-20 to +107 °C
 Material.....Steel
 Air flow.....991 L/min at 6.89 bar inlet with 0.69 bar pressure drop