

DATASHEET

Pneumatic Quick Couple, German Type, Male thread

Dimension drawing



Item No.	Model no.	L	ØD	L1	SW	MT
3594024	TC-TE7-2PM	38.2	11.9	17.7	12.7	1/4" BSP
3594025	TC-TE7-3PM	38.2	11.8	19.1	16.1	3/8" BSP
3594026	TC-TE7-4PM	41.2	11.8	21.1	20.7	1/2" BSP

Measurements for L, ØD, L1 are in mm, SW and MT are non-metric

Technical data

Working pressure Max. 10 bar

Temperature range -20 to +107 °C

Material Steel

Air flow 991 L/min at 6.89 bar inlet with 0.69 bar pressure drop