



MUV USB (AC30 PD)

Innovative 2-pole world travel adapter
with integrated Dual USB Charger (1x USB C & 1 x USB)

With the World Adapter MUV USB (AC30PD) from SKROSS® travellers from all over the world can charge a USB C device as well as a regular USB device while connecting one unearthed 2-pole device simultaneously. The travel adapter comes in an appealing compact shape and can be used in more than 220 destinations worldwide.


Suitable for



Compatibility (Input)



Compatible with the following socket types



Packaging (Retail)



Product Category

- World Travel Adapter: MUV series

Technical Specifications

- Designed in Switzerland
- Suitable for equipment with unearthed plugs (2-pole)
- Input plugs: Euro, Australia/China, UK (*not in the Swiss version), USA/Japan
- Output plugs: Euro, Australia/China, UK, USA/Japan
- Input voltage: 100 – 250 V AC, 50/60 Hz
- Max. load: 2.5 A
- Power rating: e.g. 100 V AC – 250 W / 250 V AC – 625 W
- Replaceable fuse: T 2.5 A
- 1 x Type-C USB Output: 5.0 – 20.0 V DC / Max. 3.0 A, Max. 30.0 W PD
- 1 x Type-A USB Output: 5.0 – 12.0 V DC / Max. 3.0 A, Max. 18.0 W
- Double Port Output (A+C): 5.0 V DC / 3.0 A (shared), Max. 15.0 W
- Average active efficiency: 86.2%
- Efficiency at low load (10 %): 81.0 %
- No-load power consumption: 0.06 W
- Does not convert voltage

Weight

- Adapter: 158 g (net)
- Adapter + packaging: 240 g (gross)
- Master carton: 5528 g (gross)
- Inner carton: 1312 g (gross)

Dimensions

- Adapter: 62x55x76 mm (WxHxD)
- Adapter + packaging: 103x110x72 mm (WxHxD)
- Master carton: 390x250x270 mm (LxWxH)
- Inner carton: 374x114x125 mm (LxWxH)

Standard Colour

- White

Description	Article-No.	Sales Unit / Inner / Master carton EAN-Code	Qty per Inner / Master carton / Pal	HS Code	Made in
MUV USB (AC30PD), retail, white	1.302974	7640326820864 / 7640326820888 / 7640326820871	5 / 20 / 900	8504 4060	Thailand