

Transfer or duplication of this document as well as the utilization or communication of its contents are prohibited unless explicit authorization is granted. Violations will be liable for compensation. All rights reserved for patent, utility model or design registrations. 除专利及外观设计注册外, 未经授权, 复制或传播本文件内容, 或把本文件内容用于任何形式, 均属侵权行为, 侵权者将承担相关法律责任。

FOR-1755 Rev.2.3

2




3

4

5




6

PCB LAYOUT



未注公差/General tolerances (mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	0.1/10 ±2'
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	



6	Pin header	Copper	Sn Plated
5	Spring	Stainless steel	/
4	Slider	Stainless steel	/
3	Lever	PA66-GF	UL94V-0
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

UL 标准/UL Standard:	B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)	300/20	/	300/10
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree	III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)	320/32	400/32	630/20
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	4	4	4
线径范围(硬线和软线)/Wire Range(rigid and flexible)(AWG/mm²)	24~12 / 0.2~4		
冷压头不带绝缘套管/with ferrule without plastic sleeve	24~14 / 0.25~2.5		
冷压头带绝缘套管/with ferrule, with plastic sleeve	24~14 / 0.25~2.5		
间距/Pitch(mm)/线数范围/Poles	5.0/N=01~12P		
剥线长度/Stripping length(mm)	9~11		
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		

 DEGSON			MATERIAL:		SURFACE/COLOR:										
			MAT NO. /REV:		/ 00										
			MAT STATUS: work												
APPD:			NAME DG2204R-5. 0-XXP-1Y-100Z (H)												
CHKD:															
DRFT: 陈招			2025. 09. 11		DRAWING NO.		TYPE		DRAWING STATUS		SCALE		SHEET		
 A4						200377466		CUSTOMER DRAWING		work		2:1		1/1	

00					
REV	ECN	DESCRIPTION	DRFT	DATE	

1

2

3

4

5

6