



未注公差/General tolerances(mm)													0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500 ~ ±2'
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50



2	Screw	Steel	Ni Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
间距/Pitch(mm)/线数范围/Poles			9.00/N=02~03P
使用温度范围/Operating temperature(°C)			-40~+105
符合RoHS环保要求/Conform to RoHS			Yes

			MATERIAL:		SURFACE/COLOR:			
			MAT NO./REV:		MAT STATUS: 小批量			
APPD: 蓝贵凡			2024.07.05		NAME DGBSC-ACC03-XXP-1Y-00Z(H)			
CHKD: 朱伟明			2024.07.05					
DRFT: 孙科豪			2024.07.05					
DRAWING NO.			TYPE		DRAWING STATUS		SCALE	SHEET
200290066			CUSTOMER DRAWING		已发布		1:1	1/1

00	REV	ECN	DESCRIPTION	DRFT	DATE
----	-----	-----	-------------	------	------